



Postbus 2151                      Pascallaan 9  
 8203 AD Lelystad              8218 NJ Lelystad  
 Tel: 0320-266171              Fax: 0320-257354  
 email: laboratorium@dijkstra.net  
 www.dijkstra.net

### C-MAG HP 10 IKATHERM®

New hotplate made of ceramic glass which offers excellent chemical resistance.

- Fixed safety circuit of 550 °C
- Hot Top indicator >> hot surface warning to prevent burns!
- Exact temperature setting via digital display (LED)
- Bushing according to DIN 12878 for connecting a contact thermometer, e.g. ETS-D5, enables precise temperature control
- Digital error code display
- Elevated control panel for protection against leaking liquids

Accessories: ETS-D5, H 38 Holding rod, H 44 Boss head clamp, H 16 V Support rod

Technical Data	
Number of heating points	1
Heat output [W]	1500
Heating temperature range [°C]	50 - 500
Heat control	LED
Heat control accuracy [±K]	10
Connection for ext. temperature sensor	ETS-D 4 fuzzy
Control accuracy with sensor [±K]	3
Temperature constancy in medium [±K]	3
Heating rate (1 l H <sub>2</sub> O in H15) [K/min]	5
Set-up plate material	ceramic
Set-up plate dimensions [mm]	260 x 260
Dimensions (W x H x D) [mm]	300 x 105 x 415
Weight [kg]	6
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230
Frequency [Hz]	50/60
Power input [W]	1505
<b>Ident. No.</b>	<b>3582000</b>